



BFC240F

Add-on block 1P+N 40A 300mA AC

Technical Features

Architecture

Neutral position	Left
Number of poles	2

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U_e	230 - 230 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	300 mA
Rated current	40 A

Connectivity

Down connection alignment for modular devices	Shifted terminal
---	------------------

Installation, mounting

Nominal tightening torque	1.90 - 1.90 Nm
Nominal tightening torque down terminal	1.90 - 1.90 Nm

Dimensions

Height	93.40 mm
Width	17.70 mm
Depth	66 mm

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

