



Technical Features

Neutral position	Left
Number of poles	2

Number of modules	1
-------------------	---

Rated operational voltage U_e	230 - 230 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency	50 - 50 Hz
-----------	------------

Rated residual operating current I _{dn}	300 mA
Rated current	40 A

Down connection alignment for modular devices Shifted terminal

Height	93.40 mm
Width	17.70 mm
Depth	66 mm

RoHS conform	Yes
--------------	-----