



WMCC50N

**Cooker Control Unit with LED Indicator**

**Technical Features**

**Electric current**

Rated current	45 A
---------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	White
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

**Dimensions**

Height	86 mm
Width	146 mm
Depth	39.60 mm
Built-in depth flush-mounted boxes	46 mm

**Connection**

Conductor cross-section	16 - 16 mm <sup>2</sup>
-------------------------	-------------------------

**Installation, mounting**

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	Yes

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	0
-------------------	---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Functions**

With orientation lighting	No
With function lighting	Yes

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads

**Sustainability**

RoHS conform	Yes
--------------	-----