



VA36D

Encl.,Volta,surface,3x12MOD,IP30,Version France

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	63 A
---------------	------

**Power**

Maximum power loss per cabinet at $\Delta T=20K$	17 W
--	------

**Equipment**

Number of rails	3
Number of rows	3
Number of section in width	1
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	36
Number of half modules terminals per rail	72

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	515 mm
Width	305 mm
Depth	96.50 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	0

**Dimensions**

Number of width units	12
-----------------------	----

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has mounting plate	Yes
--------------------	-----

**Materials**

Ultraviolet-resistant	Yes
-----------------------	-----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Snap on lock Without lock
Glow wire test	750 °C

---

**Sustainability**

---

RoHS conform

Yes