



WFCC50NBSW

**45A Cooker Control Unit Brushed Steel White Insert**

**Technical Features**

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 45 A |
|---------------|------|

**Materials**

|                |                 |
|----------------|-----------------|
| Colour         | Stainless steel |
| Surface finish | Matt            |
| Material       | Stainless steel |
| Treatment      | Brushed         |

**Dimensions**

|        |          |
|--------|----------|
| Height | 86 mm    |
| Width  | 146 mm   |
| Depth  | 39.60 mm |

**Connection**

|                         |                         |
|-------------------------|-------------------------|
| Conductor cross-section | 16 - 16 mm <sup>2</sup> |
|-------------------------|-------------------------|

**Installation, mounting**

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Horizontal     |

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type      | Screw mounting |

**Equipment**

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |
| With signal lamp                  | Yes              |

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Functions**

|                           |     |
|---------------------------|-----|
| With orientation lighting | No  |
| With function lighting    | Yes |

**Texts**

|            |                              |
|------------|------------------------------|
| Imprint    | Without imprint              |
| Cover      | Full cover plate             |
| Wiring     | With double earth connection |
| Protection | To protect downstream loads  |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|