



50763552



Push-button, change-over contact surface-mtd, W.1, p. white, matt, plastic

**Technical Features**

**Electric current**

Momentary contact current 10 A

**Voltage**

Rated voltage 250 V

**Materials**

Colour Polar white

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

**Dimensions**

Height 55 mm

Width 55 mm

Depth 41 mm

Built-in depth flush-mounted boxes 0 mm

Height of P-touch band for labelling field 12 mm

**Installation, mounting**

Mounting on Surface mounting

**Controls and indicators**

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

**Safety**

Ingress Protection (IP) class IP55

Impact resistance IK IK05

**Accessories**

Has labelling field Yes

**Use conditions**

Operating temperature -25 - 35 °C

**Texts**

Imprint Without imprint

Installation mode For screw fastening

Lighting With blue 230 V LED unit

Sealing With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Terminal With Wago clip-in 2-wire connection terminal for wiring  
With two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection With N-terminal  
With plug-in terminals