



1088710300

Centre plate rotary knob 3-step switch, Berker K.5, alu, aluminium anodised

Technical Features

Architecture

| | |
|---------------------------|----------|
| Control/operation element | Rotative |
|---------------------------|----------|

Materials

| | |
|----------------|-----------|
| Colour | Aluminium |
| RAL code | 9006 |
| Surface finish | Matt |
| Material | Aluminium |
| Treatment | Anodised |

Dimensions

| | |
|--------|-------|
| Height | 70 mm |
| Width | 55 mm |
| Depth | 20 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|-------------------|---------------------|
| Imprint | With imprint |
| Installation mode | For screw fastening |

Identification

| | |
|----------------------|---------------------|
| Assembly arrangement | Central cover plate |
|----------------------|---------------------|

Suitable for

| | |
|-----|--|
| K.x | |
|-----|--|