



16616049

Rocker f. access. const., guide f. mouth-held rod, lens, Q.1/Q.3, p.white velv.

Technical Features

Architecture

| | |
|---------------------------|-------------------------------|
| Control/operation element | Rocker with mouth rod guiding |
|---------------------------|-------------------------------|

Materials

| | |
|----------------|-------------|
| Colour | Polar white |
| RAL code | 9010 |
| Surface finish | Velvety |
| Material | Duroplastic |
| Treatment | Untreated |

Dimensions

| | |
|--------|----------|
| Height | 58.50 mm |
| Width | 58.50 mm |
| Depth | 22.50 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Clamp mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|-----|
| Monitoring window/light outlet | Yes |
|--------------------------------|-----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP44 |
| Impact resistance IK | IK02 |

Texts

| | |
|----------------------------------|---|
| Imprint | Without imprint |
| Installation mode | Clamp fastening |
| Lighting | For lighting and monitoring circuit |
| Push button | Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang |
| Rocker switch/rocker push-button | For rocker push-buttons For change-over/intermediate switch |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |