



VA48D

Encl., Volta, surface, 4x12MOD, IP30, Version France

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Power

Maximum power loss per cabinet at $\Delta T=20K$	20.50 W
--	---------

Equipment

Number of rails	4
-----------------	---

Number of rows	4
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	No
----------------------------	----

Capacity

Number of modules	48
-------------------	----

Number of half modules terminals per rail	96
---	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	640 mm
--------	--------

Width	305 mm
-------	--------

Depth	96.50 mm
-------	----------

Cover, door

Number of cabinet doors	1
-------------------------	---

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
----------	---------

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Equipment

Has mounting plate	Yes
--------------------	-----

Materials

Ultraviolet-resistant	Yes
-----------------------	-----

Safety

Protection class	Isolation class II
------------------	--------------------

Impact resistance IK	IK07
----------------------	------

Ingress Protection (IP) class	IP30
-------------------------------	------

Locking type	Snap on lock Without lock
--------------	------------------------------

Glow wire test	750 °C
----------------	--------

Product Datasheet
VA48D

Sustainability	
RoHS conform	Yes