



BF325

Earth leakage add-on block 3P 25A 300mA A high immunity Class

Technical Features

Electric current

Rated current	25 A
Rated residual operating current I_{dn}	300 mA

Architecture

Number of poles	3
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Capacity

Number of modules	2
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Total power loss under I_N	3 W
------------------------------	-----

Installation, mounting

Nominal tightening torque	1.70 - 1.70 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Voltage

Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Connection

Cross-section of input and output with screws, for massive conductors	1 - 10 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 6 mm ²

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	70 mm
Width	35 mm
Depth	92 mm

Illustrations | Drawings

