



BF326N

Earth leakage add-on block 3P 25A 300mA AC Class

Technical Features

Architecture

Neutral position	Right
Number of poles	3

Capacity

Number of modules	3
-------------------	---

Voltage

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I <sub>dn</sub>	300 mA
Rated current	25 A

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	70 mm
Width	35 mm
Depth	92 mm