

**15A SINGLE SWITCHED SOCKET, Noble Bronze**

**Technical Features**

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Electric current**

|                |      |
|----------------|------|
| Output current | 0 mA |
|----------------|------|

|               |      |
|---------------|------|
| Rated current | 15 A |
|---------------|------|

**Voltage**

|                |       |
|----------------|-------|
| Output voltage | 0-0 V |
|----------------|-------|

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Power**

|              |     |
|--------------|-----|
| Output power | 0 W |
|--------------|-----|

|                           |     |
|---------------------------|-----|
| Power consumption standby | 0 W |
|---------------------------|-----|

**Materials**

|        |        |
|--------|--------|
| Colour | Bronze |
|--------|--------|

|                |      |
|----------------|------|
| Surface finish | Matt |
|----------------|------|

|          |                    |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

|           |        |
|-----------|--------|
| Treatment | Coated |
|-----------|--------|

|                                                        |     |
|--------------------------------------------------------|-----|
| Contains recycled material (% of total plastic weight) | 0 % |
|--------------------------------------------------------|-----|

**Dimensions**

|        |         |
|--------|---------|
| Height | 39.5 mm |
|--------|---------|

|       |       |
|-------|-------|
| Width | 86 mm |
|-------|-------|

|       |       |
|-------|-------|
| Depth | 22 mm |
|-------|-------|

**Cable**

|              |     |
|--------------|-----|
| Cable length | 0 m |
|--------------|-----|

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
|------------------------------------|-------|

|                |       |
|----------------|-------|
| Built-in depth | 22 mm |
|----------------|-------|

**Connection**

|                     |                  |
|---------------------|------------------|
| Connector/plug type | British Standard |
|---------------------|------------------|

|                                                          |                          |
|----------------------------------------------------------|--------------------------|
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm <sup>2</sup> |
|----------------------------------------------------------|--------------------------|

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

|                               |      |
|-------------------------------|------|
| Mounting-/Connection Position | Back |
|-------------------------------|------|

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

|                    |    |
|--------------------|----|
| With claw mounting | No |
|--------------------|----|

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

|                         |                  |
|-------------------------|------------------|
| Connector/plug type USB | British Standard |
|-------------------------|------------------|

**Equipment**

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
|-----------------------------------|------------------|

|                        |    |
|------------------------|----|
| Rotated central insert | No |
|------------------------|----|

|                 |    |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

|                                 |    |
|---------------------------------|----|
| With round protective earth pin | No |
|---------------------------------|----|

|                  |    |
|------------------|----|
| With signal lamp | No |
|------------------|----|

|           |    |
|-----------|----|
| With lock | No |
|-----------|----|

---

**Accessories**

|                     |      |
|---------------------|------|
| Has labelling field | No   |
| Pre-equipped with   | None |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

**Safety**

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | No   |
| Impact resistance IK             | IK02 |
| Ingress Protection (IP) class    | IP20 |

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

**Suitable for**

|       |  |
|-------|--|
| shark |  |
|-------|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |