

15A SINGLE SWITCHED SOCKET, Aurora Silver

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Output current	0 mA
----------------	------

Rated current	15 A
---------------	------

Voltage

Output voltage	0-0 V
----------------	-------

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Output power	0 W
--------------	-----

Power consumption standby	0 W
---------------------------	-----

Materials

Colour	Aurora silver
--------	---------------

Surface finish	Matt
----------------	------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Coated
-----------	--------

Contains recycled material (% of total plastic weight)	0 %
--	-----

Dimensions

Height	39.5 mm
--------	---------

Width	86 mm
-------	-------

Depth	22 mm
-------	-------

Cable

Cable length	0 m
--------------	-----

Dimensions

Built-in depth flush-mounted boxes	35 mm
------------------------------------	-------

Built-in depth	22 mm
----------------	-------

Connection

Connector/plug type	British Standard
---------------------	------------------

Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm ²
--	--------------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Mounting-/Connection Position	Back
-------------------------------	------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

With claw mounting	No
--------------------	----

Mounting type	Screw mounting
---------------	----------------

Connector/plug type USB	British Standard
-------------------------	------------------

Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

With lock	No
-----------	----

Accessories

Has labelling field	No
Pre-equipped with	None

Capacity

Number of modules	0
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Suitable for

shark	
-------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes