



WMPS3PIF

3 Pole Isolator Switch with Fan Symbol

Technical Features

Electric current	
Switching current	10 A

Installation, mounting	
Mounting on	Flush mounting Surface mounting

Voltage	
Rated voltage	250 V

Materials	
Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification	
Assembly arrangement	Basic element with full cover plate

Connectivity	
Mounting type	Screw mounting

Controls and indicators	
Number of buttons	1

Dimensions	
Dimensions	86 x 86 mm
Built-in depth	13.10 mm

Safety	
Ingress Protection (IP) class	IP20

Architecture	
Control/operation element	Single rocker

Electric current	
Rated current	10 A

Texts	
Lighting	Without lighting (cannot be illuminated)
Switch mode	3-pole

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes