



RED013X



Power supply 28 VDC/1.25 A RMD light grey

Technical Features

Capacity

Number of modules	3
-------------------	---

Dimensions

Height	93 mm
Width	52 mm
Depth	68 mm

Connection

Number of connectable participants	32
------------------------------------	----

Use conditions

Operating temperature	5 - 40 °C
-----------------------	-----------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Voltage

Input voltage	230 - 230 V
Output voltage	28 - 28 V
Operating voltage	230 - 230 V

Electric current

Output current	1250 mA
----------------	---------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Junction	Input voltage Output voltage
----------	---------------------------------