

**15A SINGLE SWITCHED SOCKET, Knight black**

**Technical Features**

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Electric current**

|                |      |
|----------------|------|
| Output current | 0 mA |
| Rated current  | 15 A |

**Voltage**

|                |       |
|----------------|-------|
| Output voltage | 0-0 V |
|----------------|-------|

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Power**

|                           |     |
|---------------------------|-----|
| Output power              | 0 W |
| Power consumption standby | 0 W |

**Materials**

|                                                        |                    |
|--------------------------------------------------------|--------------------|
| Colour                                                 | Knight black       |
| Surface finish                                         | Matt               |
| Material                                               | Polycarbonate (PC) |
| Treatment                                              | Coated             |
| Contains recycled material (% of total plastic weight) | 0 %                |

**Dimensions**

|        |         |
|--------|---------|
| Height | 39.5 mm |
| Width  | 86 mm   |
| Depth  | 22 mm   |

**Cable**

|              |     |
|--------------|-----|
| Cable length | 0 m |
|--------------|-----|

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth                     | 22 mm |

**Connection**

|                                                          |                          |
|----------------------------------------------------------|--------------------------|
| Connector/plug type                                      | British Standard         |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm <sup>2</sup> |

**Installation, mounting**

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Back           |

**Connectivity**

|                         |                  |
|-------------------------|------------------|
| Type of connection      | Screw terminal   |
| With claw mounting      | No               |
| Mounting type           | Screw mounting   |
| Connector/plug type USB | British Standard |

**Equipment**

|                                   |                  |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert            | No               |
| With hinged lid                   | No               |
| With round protective earth pin   | No               |
| With signal lamp                  | No               |
| With lock                         | No               |

---

**Accessories**

|                     |      |
|---------------------|------|
| Has labelling field | No   |
| Pre-equipped with   | None |

---

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

---

**Safety**

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | No   |
| Impact resistance IK             | IK02 |
| Ingress Protection (IP) class    | IP20 |

---

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

---

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

---

**Suitable for**

|       |  |
|-------|--|
| shark |  |
|-------|--|

---

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |