



WGMT2RJ

**RJ11 outlet (2mod)**

**Technical Features**

**Frequency**

|                        |           |
|------------------------|-----------|
| Transmission bandwidth | 0-100 MHz |
|------------------------|-----------|

**Equipment**

|                               |    |
|-------------------------------|----|
| With transparent label holder | No |
| Number of outputs             | 2  |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

**Equipment**

|                 |    |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

**Materials**

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

**Connection**

|                     |      |
|---------------------|------|
| Connector/plug type | RJ45 |
|---------------------|------|

**Materials**

|          |                    |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Voltage**

|               |     |
|---------------|-----|
| Rated voltage | 0 V |
|---------------|-----|

**Electric current**

|               |     |
|---------------|-----|
| Rated current | 0 A |
|---------------|-----|

**Dimensions**

|                |       |
|----------------|-------|
| Built-in depth | 27 mm |
|----------------|-------|

**Texts**

|                                  |                       |
|----------------------------------|-----------------------|
| Supporting plate/supporting ring | With supporting plate |
|----------------------------------|-----------------------|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|