



BF163T

Earth leakage add-on-block 3P 63A 300mA A Class 1mod Electronic

Technical Features

Voltage

Rated operational voltage U_e	240 - 415 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	300 mA
Rated current	63 A

Architecture

Number of poles	3
Neutral position	Right

Capacity

Number of modules	1
-------------------	---

Dimensions

Width	70.80 mm
Depth	69.10 mm

Sustainability

RoHS conform	Yes
--------------	-----