



BF163T

Earth leakage add-on-block 3P 63A 300mA A Class 1mod Electronic

Technical Features

Voltage

| | |
|-------------------------------------------|-------------|
| Rated operational voltage U_e | 240 - 415 V |
| Rated insulation voltage U_i | 500 V |
| Rated impulse withstand voltage U_{imp} | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Electric current

| | |
|-------------------------------------------|--------|
| Rated residual operating current I_{dn} | 300 mA |
| Rated current | 63 A |

Architecture

| | |
|------------------|-------|
| Number of poles | 3 |
| Neutral position | Right |

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Dimensions

| | |
|-------|----------|
| Width | 70.80 mm |
| Depth | 69.10 mm |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|