



WPPS12

10AX 1 Gang 2 Way Wall Switch & Back Box without Knockouts

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Grey

Surface finish Glossy

Material Steel

Treatment Epoxy

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 0 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Texts

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way

Sustainability

REACH-SVHC free Yes

RoHS conform Yes