



FL368B

**Polyester double enclosure, Orion.Plus, plain door 2050x1100x300 mm**

**Technical Features**

**Dimensions**

Height	2050 mm
Width	1100 mm
Depth	300 mm
Thickness of sidewall	2 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	Barrel lock Key lock
Impact resistance IK	IK08

**Equipment**

Number of section in width	2
Number of flange plate openings	0

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester

**Equipment**

Number of rows	12
----------------	----

**Cover, door**

Number of cabinet doors	0
Door/cover is transparent	No

**Electric current**

Rated current	630 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----