



47357004

**SCHUKO soc. out., enhncd contact prot., K.5, stainless steel, metal matt finish**

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Stainless steel
RAL code	9022
Surface finish	Matt
Material	Metal
	Stainless steel

##### Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

##### Connection

Connector/plug type	Plug clamp
---------------------	------------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting
	Claw mounting

##### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Central cover plate

**Texts**

Protection	Enhanced contact protection
Type of connection	With plug-in terminals

**Suitable for**

K.x	
-----	--

**Sustainability**

Halogen free	Yes
RoHS conform	Yes