



WGCXS213SEG

13A TWIN SWITCHED SOCKET, EG

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	13 A
---------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Gold
Surface finish	Matt

Dimensions

Height	86 mm
Width	146 mm
Depth	28 mm

Equipment

Rotated central insert	No
With hinged lid	No

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes