



WMGSD1L

Grid Dimmer Switch Leading Edge

Technical Features

Voltage

Operating voltage 240 - 240 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

Material Urea formaldehyde

Dimensions

Height 60 mm

Width 24 mm

Depth 40 mm

Architecture

Control/operation element Push & rotative switch

Capacity

Number of modules 1

Texts

Dimming principle Phase cut-on

Installation mode Installation in surface-mounted or flush-mounted housings

Type of connection With screw terminals

Operation and control No Bluetooth interface

Sustainability

REACH-SVHC free Yes

RoHS conform Yes