



WGCXS213SNB

13A TWIN SWITCHED SOCKET, NB

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 13 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Bronze

Surface finish Matt

Dimensions

Height 86 mm

Width 146 mm

Depth 28 mm

Equipment

Rotated central insert No

With hinged lid No

Safety

Ingress Protection (IP) class IP20

Suitable for

shark

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes