



WGCXS213SNB

**13A TWIN SWITCHED SOCKET, NB**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 13 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Bronze

Surface finish Matt

**Dimensions**

Height 86 mm

Width 146 mm

Depth 28 mm

**Equipment**

Rotated central insert No

With hinged lid No

**Safety**

Ingress Protection (IP) class IP20

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes