



WRCC50NBSB

45A Cooker Control Unit Brushed Steel Black Insert

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	45 A
---------------	------

Materials

Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed

Dimensions

Height	86 mm
Width	146 mm
Depth	39.60 mm

Connection

Conductor cross-section	16 - 16 mm ²
-------------------------	-------------------------

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	Yes

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	Yes

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads

Sustainability

RoHS conform	Yes
--------------	-----