
Product Datasheet
1394



1394

Glass cover plate 4gang TS polar white glossy

Technical Features

Capacity

Number of gangs	4
Number of modules	4

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Glass
Treatment	Untreated

Dimensions

Height	160 mm
Width	86 mm
Depth	5 mm

Accessories

Has labelling field	No

Installation, mounting

Mounting-/Connection Position	Horizontal Vertical

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Texts

Installation mode	Clamp fastening For vertical and horizontal mounting
Screws/screwdriver	Each with 2 M3.5 x 25 mm two-hole screws in chrome, gold and stainless steel for dismantling protection With screwdriver

Sustainability

Halogen free	Yes
RoHS conform	Yes