



WXF436N

Switch 16AX multi sockets gallery night

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Jet black
RAL code	9005
Surface finish	Satin finish
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Mechanism with upper casing
----------------------	-----------------------------

Connectivity

Mounting type	Click mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	45 x 45 mm
Built-in depth	52 mm
Built-in depth flush-mounted boxes	40 mm

Safety

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

Electric current

Rated current	16 A
---------------	------

Texts

Lighting	Can be illuminated by status LED
Switch mode	2-pole off