



VB318W

Small distributor, vega, surface, 3row, 54M, IP40, QC-terminal, PE, transparent door

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	3
Number of rows	3
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	54
-------------------	----

**Dimensions**

Height	625 mm
Width	400 mm
Depth	146 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	1

**Dimensions**

Number of width units	18
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Materials**

Material	Polystyrene (PS)
RAL code	9010
Colour	White

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

**Sustainability**

RoHS conform	Yes
--------------	-----