



WNC003

IP55

cubyko 2-way switch with control light with neutral wall mounted grey IP55

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Grey

RAL code 7011

Surface finish Matt
Satin finish

Material Thermoplastic

Treatment Untreated

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 76 x 76 mm

Built-in depth 65 mm

Built-in depth flush-mounted boxes 0 mm

Height of P-touch band for labelling field 0 mm

Safety

Impact resistance IK IK08

Usable in higher IP class IP55 with closed cover

Electric current

Rated current 10 A

Connection

Type of contacts 2-way

Connector/plug type Plug-in terminal

Texts

Installation mode For screw fastening

Type of connection With N-terminal
With plug-in terminals

Lighting With red 230 V LED unit
For monitoring circuit

Push button No

Imprint Without imprint

Sustainability

REACH-SVHC free Yes