



TRE510



Motion detector radio, IP55, surface mounted, white

Technical Features

Dimensions

Installation height	4 - 4 m
---------------------	---------

Settings

Supported configuration mode	ETS easy
Minimal duty cycle	5 s

Functions

Maximal duty cycle	30 min
--------------------	--------

Connectivity

With bus system KNX radio	Yes
---------------------------	-----

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Detection

Detection angle adjustable	45 - 90 °
Detection angle horizontal	220 - 220

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC)
----------	---

Texts

Function	Switch-off pre-warning on dimmer inserts With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours Reset function (to factory setting)
----------	---

Reach distance

Max. transmission range frontally	16 m
Max. transmission range sideways	10 m