



4504

Light switch 8A, compact basic

Technical Features

Voltage

Rated operational voltage U_e 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Power

230 V incandescent and halogen lamp 1000 W

Settings

Switch off delay time 120 s

Switch on delay time 40 s

Use conditions

Storage/transport temperature -30 - +60 °C

Connection

Cross-section flexible conductor 1 - 4 mm²

Cross-section rigid conductor 1 - 4 mm²

Texts

Installation mode With pipe clamp for mast fixing
Installation possible on flush-mounted box
For wall and mast assembly

Type of connection With screw terminals

Electric current

Switching current 8 A

Dimensions

Height 95 mm

Width 80 mm

Depth 42.50 mm

Sustainability

REACH-SVHC free Yes

RoHS conform Yes