



WNA686B

cubyko Double vertical box empty white IP55

Technical Features

Capacity

Number of modules	2
-------------------	---

Materials

Colour	Polar white
RAL code	9010
Surface finish	Mat
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	147 mm
Width	76 mm
Depth	56 mm

Equipment

With cable entry	Yes
------------------	-----

Installation, mounting

Mounting-/Connection Position	Vertical
Mounting on	Surface mounting

Accessories

With frame cover	Yes
------------------	-----

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	For vertical mounting
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Suitable for

Hager cubyko	
cubyko	

Sustainability

Halogen free	Yes
REACH conform	Yes
RoHS conform	Yes