



MH4003S4

Technical Features

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Voltage

Nominal voltage	415 - 415 V
-----------------	-------------

Electric current

Rated current	400 A
---------------	-------

Dimensions

Depth	153 mm
Internal depth	148 mm
Height	916 mm
Width	416 mm
Thickness of sidewall	1.20 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9002
Colour	Grey white
Material	Steel

Connection

Number of conduit inlets	10
--------------------------	----

Equipment

Number of rails	0
Extension possible	No
With bell transformer	No
With socket outlet	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP20
Protection class	Isolation class I

Sustainability

REACH-SVHC free	Yes
-----------------	-----