



VF312TT2

Small distributor,golf,flush,3row,36M,IP40,MS-terminal,ANZ,N+PE,transparent door

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

#### Electric current

Rated current	80 A
---------------	------

#### Equipment

Number of rails	3
Number of rows	3
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	36
-------------------	----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	543 mm
Width	352 mm
Depth	97.50 mm
Built-in height	507 mm
Built-in width	318 mm

#### Cover, door

Number of cabinet doors	1
-------------------------	---

#### Dimensions

Built-in depth	72 mm
----------------	-------

#### Cover, door

Number of locks	0
-----------------	---

#### Dimensions

Number of width units	12
-----------------------	----

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Materials

Ultraviolet-resistant	No
-----------------------	----

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Safety

Locking type	Snap on lock
	Without lock
Glow wire test	650 °C

Sustainability

RoHS conform	Yes
--------------	-----