



WBP2VS

Premiere 10A vert twin GPO

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Output voltage	5 - 5 V
----------------	---------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
--------	-------

Dimensions

Height	77 mm
--------	-------

Width	117 mm
-------	--------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Connector/plug type USB	AA
-------------------------	----

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
-----------------------------------	---------------------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Texts

Imprint	Without imprint
---------	-----------------

Fuse	Short-circuit and overload-proof (electronic fuse)
------	--

Cover	Full cover plate
-------	------------------

Connectors jacks	With 2 USB sockets type A
------------------	---------------------------

Suitable for

premiere	
----------	--

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----