



WBP2VS

Premiere 10A vert twin GPO

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Output voltage	5 - 5 V
----------------	---------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
--------	-------

Dimensions

Height	77 mm
Width	117 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Mounting type	Screw mounting
Connector/plug type USB	AA

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Fuse	Short-circuit and overload-proof (electronic fuse)
Cover	Full cover plate
Connectors jacks	With 2 USB sockets type A

Suitable for

premiere	
----------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes