




FL310B

Polyester wall mounting enclosure, Orion.Plus, plain door 550x1100x300 mm

Technical Features

Dimensions

Height	550 mm
Width	1100 mm
Depth	300 mm
Thickness of sidewall	1.50 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

Equipment

Number of section in width	2
Number of flange plate openings	0

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Plastic

Equipment

Number of rows	3
----------------	---

Cover, door

Number of cabinet doors	0
Door/cover is transparent	Yes

Electric current

Rated current	630 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----