



VS418TJ

Small distributor,golf,surface,4row,IP40,72M,MS-terminal,N+PE,transparent door

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	4
Number of rows	4
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	72
-------------------	----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	647 mm
Width	390 mm
Depth	99 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	0

#### Dimensions

Number of width units	18
-----------------------	----

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Materials

Ultraviolet-resistant	No
-----------------------	----

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

#### Sustainability

RoHS conform	Yes
--------------	-----