



KH25C



Glavna razdjelna klema, 5P, 2x25/2x16mm²

Tehničke karakteristike

Dimenzije

Visina	65,90 mm
Širina	102,40 mm
Dubina	45,50 mm

Veza

Presjek krutog provodnika	1.5 - 25 mm ²
---------------------------	--------------------------

Instalacija, montaža

Nazivni zatezni moment	2,80 - 2,80 Nm
------------------------	----------------

Električna struja

Nazivna struja	80 A
----------------	------

Arhitektura

Broj polova	5
-------------	---

Održivost

Bez halogena	Da
Usklađeno sa RoHS	Da