



FL325B

Polyester floor standing enclosure, Orion.Plus, plain door 600x850x300 mm

Technical Features

Dimensions

| | |
|-----------------------|---------|
| Height | 600 mm |
| Width | 850 mm |
| Depth | 300 mm |
| Thickness of sidewall | 1.50 mm |

Safety

| | |
|-------------------------------|-------------------------|
| Ingress Protection (IP) class | IP65 |
| Protection class | Isolation class II |
| Locking type | 3-Side 7 mm Key lock |
| Impact resistance IK | IK10 |

Equipment

| | |
|---------------------------------|---|
| Number of section in width | 1 |
| Number of flange plate openings | 2 |

Installation, mounting

| | |
|----------------------------|----------------|
| Mounting on | Floor mounting |
| Suitable for outdoor usage | Yes |

Materials

| | |
|-----------|------------|
| Colour | Light grey |
| RAL code | 7035 |
| Treatment | Untreated |
| Material | Plastic |

Equipment

| | |
|----------------|---|
| Number of rows | 3 |
|----------------|---|

Cover, door

| | |
|---------------------------|-----|
| Number of cabinet doors | 0 |
| Door/cover is transparent | Yes |

Electric current

| | |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|