



WNC021



IP55



cubyko Push-button 10/1F with light wall mounted grey IP55

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Single rocker
Number of poles	1

Materials

Colour	Grey
Surface finish	Matt Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Contains recycled material (% of total plastic weight)	24.1 %
Backside internal	Matt

Dimensions

Height	76 mm
Width	76 mm
Depth	61.50 mm
Built-in depth flush-mounted boxes	0 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Controls and indicators

Indicator lamp	As an accessory
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Installation mode	For screw fastening
Lighting	With blue 230 V LED unit For lighting and monitoring circuit
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Switch mode	Change-over

Texts

Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
----------	--

Type of connection	With N-terminal With plug-in terminals
--------------------	---

Suitable for

cubyko

Sustainability

REACH-SVHC free	Yes
-----------------	-----