



VS112TVA

**Small distributor, 12 modules, surface, 1 row, IP40, 12M, MS-terminal, N+PE, transparent door**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

With lock	No
-----------	----

Has neutral terminal block	Yes
----------------------------	-----

**Capacity**

Number of modules	12
-------------------	----

**Dimensions**

Height	165 mm
--------	--------

Width	301 mm
-------	--------

Depth	92.50 mm
-------	----------

**Cover, door**

Number of cabinet doors	1
-------------------------	---

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	12
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Materials**

Material	Plastic
----------	---------

RAL code	9010
----------	------

Colour	White
--------	-------

**Equipment**

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

**Safety**

Impact resistance IK	IK07
----------------------	------

Ingress Protection (IP) class	IP40
-------------------------------	------

Locking type	Snap on lock
--------------	--------------

Glow wire test	650 °C
----------------	--------

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----