



FL327B

Polyester floor standing enclosure, Orion.Plus, plain door 1200x850x300 mm

Technical Features

Dimensions

|                       |         |
|-----------------------|---------|
| Height                | 1200 mm |
| Width                 | 850 mm  |
| Depth                 | 300 mm  |
| Thickness of sidewall | 2 mm    |

Safety

|                               |                         |
|-------------------------------|-------------------------|
| Ingress Protection (IP) class | IP65                    |
| Protection class              | Isolation class II      |
| Locking type                  | Barrel lock<br>Key lock |
| Impact resistance IK          | IK08                    |

Equipment

|                                 |   |
|---------------------------------|---|
| Number of section in width      | 1 |
| Number of flange plate openings | 0 |

Installation, mounting

|                            |               |
|----------------------------|---------------|
| Mounting on                | Wall mounting |
| Suitable for outdoor usage | Yes           |

Materials

|           |                            |
|-----------|----------------------------|
| Colour    | Light grey                 |
| RAL code  | 7035                       |
| Treatment | Untreated                  |
| Material  | Glass reinforced polyester |

Equipment

|                |   |
|----------------|---|
| Number of rows | 7 |
|----------------|---|

Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 0  |
| Door/cover is transparent | No |

Electric current

|               |       |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|