



VS418PM

Small distributor,golf,surface,4row,IP40,72M,MS-terminal,N+PE,white door

Technical Features

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

Installation, mounting

| | |
|----------------------------|------------------|
| Suitable for outdoor usage | No |
| Mounting on | Surface mounting |

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Equipment

| | |
|----------------------------|-----|
| Number of rails | 4 |
| Number of rows | 4 |
| Number of section in width | 1 |
| With lock | No |
| Has neutral terminal block | Yes |

Capacity

| | |
|-------------------|----|
| Number of modules | 72 |
|-------------------|----|

Functions

| | |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

Dimensions

| | |
|--------|--------|
| Height | 647 mm |
| Width | 390 mm |
| Depth | 99 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks | 0 |

Dimensions

| | |
|-----------------------|----|
| Number of width units | 18 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|-------------|
| Door/cover is transparent | No |
| Cabinet door type | Single door |

Materials

| | |
|----------|------------|
| Material | Plastic |
| RAL code | 9010 |
| Colour | Pure white |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate | No |

Materials

| | |
|-----------------------|----|
| Ultraviolet-resistant | No |
|-----------------------|----|

Safety

| | |
|-------------------------------|------------------------------|
| Protection class | Isolation class II |
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |
| Locking type | Snap on lock Without lock |
| Glow wire test | 650 °C |
| Protection class with door | IP40 |

Sustainability

RoHS conform

Yes