



41102045



**SCHUKO soc.out. control LED,enhncd contact prot.,screw-in lift term.,R.1.3,bl.**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Black

RAL code 9005

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth 32 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

**Accessories**

Has labelling field Yes

**Capacity**

Number of modules 1

**Controls and indicators**

Type of lighting for the installation devices Integrated operating control light

**Safety**

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting Yes

**Identification**

With imprint No

---

**Texts**

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

---

**Suitable for**

R.x

---

**Sustainability**

Halogen free	Yes
RoHS conform	Yes