



41102089



SCHUKO soc.out. control LED,enhncd contact prot.,screw-in lift term.,R.1.3,wh

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	40.80 mm
Number of units	1
Built-in depth	32 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	Yes
---------------------	-----

Capacity

Number of modules	1
-------------------	---

Controls and indicators

Type of lighting for the installation devices	Integrated operating control light
---	------------------------------------

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	Yes

Identification

With imprint	No
--------------	----

Texts

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for

R.x

Sustainability

Halogen free	Yes
RoHS conform	Yes