



GBA501311ALU

Install. trunking-Base Alu 50131,anodised.

Technical Features

Dimensions

Height	56 mm
Width	134 mm
Length	2000 mm

Cover, door

Number of mountable lids	2
Cover width 1	45 mm
Cover width 2	45 mm
Cover width 3	0 mm

Dimensions

Inner cross-section	6500 - 6500 mm ²
---------------------	-----------------------------

Capacity

Max. number of cables (Ø11 mm, 50% filled, with devices)	15
Max. number of cables (Ø11mm, 50% filled, without devices)	37

Compatibility

Device installation compatible format	47 x 45 mm
---------------------------------------	------------

Installation, mounting

Base perforation	No
------------------	----

Materials

Material	Aluminium
Treatment	Anodised
Colour	Aluminium

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Use conditions

Operating temperature	-5 - 90 °C
-----------------------	------------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Equipment

Cable retaining clip included	No
Number of cable retainers per meter	0
With protective film	Yes

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

