



75648001



Universal input/output interface 8gang KNX

Technical Features

Settings

Supported configuration mode ETS

Electric current

Number of entry circuits 8

Equipment

External signal voltage necessary No

Connectivity

With bus system KNX radio No

Equipment

Radio frequency bidirectional No

Installation, mounting

Mounting on Flush mounting

Lighting

LED controlling Yes

Materials

Colour Black

RAL code 9005

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -5 - 45 °C

Cable

Cable length 10 m

Voltage

Input voltage 20 - 20 V

Operating voltage over bus 21 - 32 V

Type voltage supply AC/DC

Dimensions

Height 48 mm

Depth 32 mm

Texts

Type of connection With screw terminals

Sustainability

REACH-SVHC free Yes

RoHS conform Yes